

# GLA 5000 PVC Membrane Filters

Suitable for multiple NIOSH/OSHA/ASTM air sampling methods

- Silica, metals, dust
- Meets OSHA Method ID-215 (V. 2) for hexavalent chromium

Low tare weight and moisture pickup for gravimetric stability

- <0.5% after 24 hours at 48 %RH and 122°F (50°C)

Preloaded 25 and 37 mm cassettes available

- 25 mm cassettes are convenient for sampling inside a welding helmet



## PVC Cassette for Welding

Use 25 mm preloaded PVC filter part number 225-8214 or 225-8215 for sampling welder exposure to hexavalent chromium as specified in OSHA Method ID-215 (V. 2). The smaller cassette fits more easily under a welder's helmet. For ultimate comfort, use the Helmet Adaptor (part number 225-600) or the [Face Level Sampling Headset](#).

## PVC Filters

Diameter (mm)	Pore Size (µm)	Support Pad included *	Notes	Pack Size	Part Number	Article number
25	5.0	No	Recommended for use with IOM and Button Samplers	100	225-5-25	205079
37	5.0	Yes	Available in ready-to-use preloaded cassettes	100 1000	225-5-37-P 225-80601K	205081
37	5.0	No		100	225-5-37	205080
47	5.0	No		100	225-5-47	205082

\* Filter supports available

Meetapparatuur voor professionals



## GLA-5000™ PVC Filters in Preloaded Cassettes

All SKC preloaded filters include supports and are in SureSeal leak-free cassettes that require a SureSeal Cassette Opener.

Diameter (mm)	Cassette Description	Filter Specification	Pack Size	Part Number	Article number
25	Clear styrene, 2-piece, banded	5.0 µm	50	225-8214	205086
25	Clear styrene, 3-piece, banded	5.0 µm	50	225-8215	
37	Clear styrene, 2-piece, banded	5.0 µm	50	225-802	
37	Clear styrene, 3-piece, banded	5.0 µm	50	225-803	431140
37	Clear styrene, 2-piece, banded	5.0 µm, preweighed 5 decimal	12	225-8204	205056
			100	225-8205	
37	Clear styrene, 3-piece, banded	5.0 µm, preweighed 5 decimal	12	225-8208	
			100	225-8209	
37	Clear styrene, 2-piece, banded	5.0 µm, matched-weight within 25 µg	50	225-8201	
37	Clear styrene, 3-piece, banded	5.0 µm, matched-weight within 25 µg	50	225-8202	
SureSeal Cassette Opener, for opening 25 mm or 37 mm SureSeal Cassettes				225-13-5A	222013

## ACCU-CAP PVC Filters Inserts

Clear plastic capsules heat-sealed to a filter; fit between parts of a 2-piece cassette with support pad; prevent cassette wall losses

Diameter (mm)	Cassette Description	Pack Size	Part Number	Article number
37	Contains GLA-5000 PVC membrane filter, 5.0 µm pore size, for collection of fibrous and static dust for gravimetric analysis	60	225-8516GLA	

Meetapparatuur voor professionals



## Matched-weight PVC Filter

Diameter (mm)	Cassette Description	Pack Size	Part Number	Article number
37	5.0 µm, matched-weight within 25 µg, not preloaded in cassettes, filter pairs only	50	225-8222	

## Speciality PVC Filters for the Respicon™ Sampler

Diameter (mm)	Pore Size (µm)	Support Pad included *	Notes	Pack Size	Part Number	Article number
37	5.0	No	With hole for Respicon Sampler, no support pad	100	225-8990-R	

\* Filter supports available

Meetapparatuur voor professionals

**ProCare** | SAFETY  
*We take intensive Care*

[www.procaresafety.nl](http://www.procaresafety.nl) | [info@procaresafety.nl](mailto:info@procaresafety.nl)

### Locatie Groningen

Zernikepark 16a  
9747 AN Groningen  
T 050 2072172

### Locatie Amsterdam

Olympisch Stadion 24-2  
1076 DE Amsterdam  
T 020 2613999

 @ProCare\_safety

