

Filters & Cassettes



Mixed Cellulose Ester Membranes

Diameter (mm)	Pore Size (µm)	Support Pad Included	Notes	Pack Size	Part Number:
13	5.0	No	Use with Swinnex	100	225-8050
25	0.45	No		100	225-1911
25	0.8	No	Use with IOM	100	225-1930
25	0.8	No		100	225-19P
25	0.8	Yes	Use with IOM	100	225-19
25	0.8	No	Black grid, principally used for asbestos sampling in UK	100	225-1913
25	1.2	No	Cellulose, ashless, recommended for use with the Button Sampler	100	225-1912
34	0.45	No	MCE filters with radial slits for Marple Impactor	50	225-1932
37	-	No	Cellulose, ashless, Type 40	500	225-18B
37	-	No	Cellulose, ashless, Type 4	500	225-18A
37	0.45	Yes		100	225-9

Meetapparatuur voor professionals



37	0.45	No		100	225-1914
37	0.8	Yes	Available in ready-to-use preloaded cassettes	100	225-5
37	0.8	No		100	225-1939
37	0.8	No	Black grid	100	225-334
37	1.2	No		100	225-1923
37	5.0	No		100	225-1938
47	0.45	No		100	225-506
47	0.8	No		100	225-504
47	1.2	No		100	225-1921
102	0.8	No		25	225-1916

† Filter supports available

Matched-weight MCE Filters

Diameter (mm)	Filter Specifications	Pack Size	Part Number:
37	MCE, 0.8 µm, matched-weight within 50 µg, filter pairs only, not in preloaded cassettes	50 Pairs	225-532
47	MCE, 0.8 µm, matched-weight within 50 µg, filter pairs only, not in preloaded cassettes	50 Pairs	225-531

Meetapparatuur voor professionals



ACCU-CAP MCE Filter Inserts

Diameter (mm)	Pore Size (µm)	Pack Size	Part Number:
25	0.8	60	225-8506
37	0.8	60	225-8514

Specialty MCE Filters for the Respicon™ Sampler

Diameter (mm)	Pore Size (µm)	Support Pad Included	Notes	Pack Size	Part Number:
37	0.8	No	with hole for Respicon Sampler	100	225-1941
37	0.5	No	with hole for Respicon Sampler	100	225-1922

Preloaded MCE Filters

Diameter (mm)	Pore Size (µm)	Cassette Description	Pack Size	Part Number:
25	0.8	3-piece clear plastic, banded	50	225-3100
25	1.2	3-piece black conductive polypropylene (goblet style with extension cowl), banded	50	225-507
37	0.45	3-piece black conductive, banded	50	225-1924
37	0.45	4-piece clear styrene, banded, BestChek® quality tested for low asbestos fiber background; certificate of analysis included	50	225-1925
37	0.8	2-piece clear styrene, banded	50	225-508
37	0.8	3-piece clear styrene, banded	50 500	225-3-01 225-3-01A

Meetapparatuur voor professionals



37	0.8	3-piece clear styrene, not banded	50	225-3-01NB
----	-----	-----------------------------------	----	------------

Preloaded Matched-weight MCE Filter Cassettes

Diameter (mm)	Cassette Description	Filter Specifications	Matched-Weight	Pack Size	Part Number:
25	2-piece clear styrene, banded	0.8 µm MCE with support	within 50 µg	50	225-525
37	3-piece clear styrene, banded	0.8 µm MCE	within 100 µg	50	225-3-02
37	2-piece clear styrene, banded	0.8 µm MCE	within 50 µg	50	225-502
37	3-piece clear styrene, banded	0.8 µm MCE	within 50 µg	50	225-503
37	2-piece clear styrene, banded	0.8 µm MCE with support	within 50 µg	12	225-527
37	3-piece clear styrene, banded	0.8 µm MCE with support	within 50 µg	12	225-528

Specialty MCE Filters for the Marple Series 290 Cascade Impactor

Diameter (mm)	Pore Size (µm)	Support Pad Included	Notes	Pack Size	Part Number:
34	0.45	No	MCE filters with radial slits for Marple Impactor	50	225-1932

Meetapparatuur voor professionals

