

Filters & Cassettes



PTFE (Polytetrafluoroethylene) Filters

Diameter (mm)	Pore Size (µm)	Support Pad Included	Notes	Pack Size	Part Number:
13	5.0	No	unlaminated	100	225-17-03
25	0.5	No	with laminated PTFE support	100	225-2708
25	1.0	No	with laminated PTFE support	100	225-2714
25	2.0	No	with laminated PTFE support	100	225-2726
25	3.0	No	with PMP support ring †	50	225-1711
25	5.0	No	unlaminated	50	225-1728
37	0.3	No	For Anthrax/SARS, laminated spun-bound polyester, available in ready-to-use preloaded cassettes	100	225-1722
37	0.45	Yes	on polypropylene support	100	225-17-04
37	1.0	Yes	on polypropylene support	100	225-17-01
37	1.0	Yes	with laminated PTFE support	50	225-2705
37	2.0	Yes	with laminated PTFE support	50	225-27-07
37	2.0	No	with PMP support ring	50	225-1709

Meetapparatuur voor professionals



37	5.0	Yes	unlaminated	50	225-17A
37	10.0	No	unlaminated	100	225-1729
47	0.5	No	with laminated PTFE support	50	225-2753
47	1.0	No	with laminated PTFE support	50	225-2749
47	2.0	No	with PMP support ring	50	225-1747
47	2.0	No	with laminated PTFE support	50	225-2748
47	5.0	No	unlaminated	100	225-1724
47	60.0	No	unlaminated	100	225-1755

† Recommended for use with the Button Sampler

* Filter support pads available

Meetapparatuur voor professionals



Diameter (mm)	Filter and Cassette Specifications	Pack Size	Part Number:
25	PTFE, 1.0 µm with polypropylene pad preloaded in 2-piece conductive cassette, goblet style	50	225-1725
25	PTFE, 1.0 µm with polypropylene support pad preloaded in 2-piece black conductive cassette, goblet style	50	225-1751
25	PTFE, 1.0 µm with cellulose support pad preloaded in 2-piece conductive cassette, goblet style	50	225-1716
25	PTFE, 2.0-µm filters with 60-µm laminated support and polypropylene support pad preloaded in 2-piece black conductive cassette, goblet style	50	225-1750
37	PTFE, 0.3 µm, laminated with spun-bound polyester with cellulose support, unsterilized 3-piece clear styrene cassette, banded; for Anthrax/SARS	50	225-1723
37	PTFE, 1.0 µm with cellulose support, preloaded in a 3-piece, clear styrene (traditional style) cassette, banded	50	225-1715
37	PTFE, 2.0 µm with cellulose ring, 2-piece plastic cassette, banded	50	225-1713

Meetapparatuur voor professionals

Locatie Groningen

Zernikepark 16a
9747 AN Groningen
T 050 2072172

Locatie Amsterdam

Olympisch Stadion 24-2
1076 DE Amsterdam
T 020 2613999

